

Checklist for Electrical Connectors / Inquiry Form

1. General Information

Name: _____	Date: _____
Company: _____	Project-No: _____
Address: _____	Drawing-No: _____
	(drawing enclosed) yes no
Ci/St/Zip: _____	Quantity: _____
Phone: _____	Target price: _____
Fax: _____	Delivery schedule: _____
Email: _____	Other information: _____

2. Application Information (please describe your application)

3. Electrical Characteristics

Rated Current: _____	A	DC	AC - Frequency: _____	Hz
Short circuit current: _____	A (rms)		Rated voltage: _____	V
Short circ. duration: _____	s		Test voltage: _____	V
Surge current: _____	A (peak)			
Intermittent current: _____	A (peak)			
t _{on} : _____	s			
t _{off} : _____	s			
Pulse frequency: _____	Hz			
Other: _____				

4. Ambient Conditions

Air	Water	Oil	Vacuum	Gas (i.e. SF6)	Explosive
Temperature: _____				Relative humidity: _____	
Add. information: _____					

5. Mechanical Characteristics

Connector material: _____	Total mating cycles: _____
Plating type: _____	Plating thickness: _____
Withdrawal force: _____	Max. connector temp.: _____

6. Type of Connection

screw / bolted	soldered / brazed	crimped
Size: _____		

7. Material and Dimensions of Conductor

Material: _____	
Cross-section: _____	
Wire	Size: _____
Busbar	Width: _____
	Height: _____
Other information: _____	

Please go to next page

Multi-Contact USA

5560 Skylane Blvd.
Santa Rosa, CA 95403

Tel: (707) 575-7575


Fax: (707) 575-7373

Email: mailbox@multi-contact-usa.com

Checklist for Electrical Connectors / Inquiry Form

8. General Dimensions

Plug	Socket	Fork/Busbar
Plug O.D.: _____	Socket I.D.: _____	Blade thickness: _____
Socket I.D.: _____	Plug O.D.: _____	Fork width: _____
Plug width: _____	Socket width: _____	Max. fork length: _____
Max. plug length: _____	Max. socket length: _____	



Comments/Sketch Area: